



QUICK START GUIDE

VE0100-A/VE0201-A



User Manual



All software & files can be downloaded from
<https://www.milesight.com/support/download/>

Make Sensing Matter

Milesight | www.milesight.com



Table of Contents

1.Package Contents.....	2
2.Hardware Introduction.....	2
3.Interfaces.....	3
4.Installation.....	3
5.Device Connection Topology.....	8
6.Ready to Start.....	8

1. Packing List



Enterprise NVR
x1



Quick Start Guide
x1



Warranty Card
x1



2.5"HDD Screw
x8



3.5"HDD Screw
x8



Mounting Bracket
x2



Mounting Bracket Screw
x4



HDD Power Cable
x1



Power Cord
x1




Power Adapter
x1




SATA Cable x1 (Optional for VE0100-A)
SATA Cable x2 (Optional for VE0201-A)

2. Hardware Introduction




3. Interfaces




- | | | | |
|--------------|--------------------------|-------------------|------------------|
| 1. Audio | 4. HDMI Port | 7. 2*LAN Port | 10. Power Button |
| 2. USB 3.0 | 5. USB-C | 8. Power Port | |
| 3. 2*USB 2.0 | 6. DP Port and HDMI Port | 9. Restart Button | |

4. Installation


Step1: Using a cross screwdriver to remove the screws at the rear panel and side panel in an anticlockwise direction.




Step2: Slide the upper casing to the rear first and lift it up.



Step3: Secure the HDD from the bottom of the casing. 4 screws for each HDD.




(2.5" HDD Installation)




(3.5" HDD Installation)

Step4: After that, check if all the screws are tightened. Then connect the power cable and data cable to each HDD.




(Screw Position of 2.5" HDD)




(Screw Position of 3.5" HDD)


Step5: Pull down the upper casing and slide it to the front.



Step6: Lock the screws on the rear panel and side panel.



5. Device Connection Topology



6. Ready to Start

When Machine is connected to a power source, it will power up automatically (Power up recovery is enabled by default).

客 户	
机 型	VE0601-A/VE0602-A
材 质	200g铜版纸+80g双胶纸
尺 寸	120x85mm
工 艺	封面覆哑膜（翻页版）
编 码	43.005.000219
版 本	V3.0